

UP100 초음파 트랩 진단기

● 개요

UP100 / 가

● 구성품

UP100 4가

1. : 9
- 2.
- 3.
- 4.

● 사용조건

: 0~50
: - 18~54

● 기술사양

Circuitry	SMD/solid state heterodyne receiver
Frequency response	20-100 kHz (centred on 38-42 kHz)
Sensitivity selection	8 position precision attenuation
Ultrasonic level display	10 segment red LED bargraph
Battery	9 volt alkaline
Headset	Sony "Walkman" type model MDR 24 (non standard male plug)
Probes	Stethoscope/contact module type (STM-1) stainless steel plug in type with 140 mm stainless steel waveguide. Extension rods to 788 mm for inaccessible steam traps.

● 재 질

Pistol housing	ABS plastic
Probe module	Stainless steel
Extension rods	Aluminium alloy
Carrying case	Black soft cordura

● 정비 부품

가

1. 9
2. MDR24 ()
3. STM - 1
4. 788 mm

● 사용방법



● 치수(mm) 및 무게(kg)

	A	B	C	D	무게 (건전지 포함)
점검기	114	200	48	292	0.35
점검기+케이스	250 mm W x 160 mm L x 90 mm H				0.70

