

DP143, DP143G, DP143H, SDP143 DP163, DP163Y 감압밸브 정비부품

TI-P006-02
CH Issue 3
(KR 0411)

● 정비부품

정비부품명세

Maintenance kit

'*'로 표시된 정비부품이 포함되어 있음

* Main diaphragm	(2 off)		A
* Pilot diaphragm	(2 off)		B
Pilot valve seal assembly			C
* Pilot valve and plunger assembly			D, E
Main valve assembly			F, H
* Main valve return spring			G
	적색	DP143, DP143G, DP143H, SDP143, DP163	0.2 ~ 17 bar
Pressure adjustment spring	회색	DP143, DP143G, DP143H, SDP143	16 ~ 24 bar
		DP163	16 ~ 21 bar
	황색	DP163Y	0.2 ~ 3 bar
* Control pipe assembly			K
* Balance pipe assembly			M, N
* Body gasket (packet of 3)			O
Set of spring housing securing studs and nuts	(set of 4)		P
Set of pilot valve housing securing studs and nuts	(set of 4)		Q
Set of diaphragm chamber securing bolts and nuts	(set of 10)	DN15, DN20	R
	(set of 12)	DN25, DN32	
	(set of 16)	DN40, DN50	
	(set of 20)	DN80	
Set of main body studs and nuts (DN80)	(set of 6)		T
Pushrod and main diaphragm plate assembly			V

● 정비부품의 호환성

DN15LC, 15, 20

DN25, 32가

'SDP', 'G'

† DP143 DP163

Size	**							
	DN15LC	DN15	DN20	DN25	DN32	DN40	DN50	DN80
Main diaphragm	a	a	a	b	b	c	c	d
Pilot diaphragm	a	a	a	a	a	a	a	a
Pilot valve seal assembly	a	a	a	a	a	a	a	a
Pilot valve and plunger assembly	a	a	a	a	a	a	a	a
Main valve assembly	a	b	c	d	e	f	g	h
Main valve return spring	a	a	a	b	b	c	c	d
Pressure adjustment spring	a	a	a	a	a	a	a	a
† Control pipe assembly	a	a	b	c	d	e	f	g
† Balance pipe assembly	a	a	b	c	d	e	f	g
† Body gasket	a	a	a	b	b	c	c	d
† Set of spring housing securing studs and nuts	a	a	a	a	a	a	a	a
† Set of pilot valve housing securing studs and nuts	a	a	a	b	b	c	c	d
† Set of diaphragm chamber securing bolts and nuts	a	a	a	b	b	c	c	d
† Set of main body studs and nuts	-	-	-	-	-	-	-	a

** DP143G에서는 이용할 수 없다.

