

A.2.1 (kg/h)

( 50m , 20 , 80% )

(\*)

가

(bar g)	(mm)														-18
	50	65	80	100	125	150	200	250	300	350	400	450	500	600	
0	4.2	6.6	8.7	12.4	16.8	21.2	32.7	46	61	73	95	120	141	142	1.5
0.3	4.7	7.5	9.8	14	18.4	24.5	37	52.5	69	82	107	135	154	220	1.44
0.6	5.1	8	10.6	15	20.4	26.5	39.5	56.6	74	88	115	145	171	238	1.41
	4.1	4.7	6.1	7.5	8.9	10.9	13.6	16.4	19.8	22	24	26	30	36	1.58
1	5.4	8.6	11.2	16	21.7	28.2	43.6	60	79.4	94	123	155	182	254	1.39
	4.8	5.4	6.8	8.5	10.3	12.8	15.8	19.2	22.9	25	28	31	35	41	1.54
2	6.2	10	13	18.5	25	32.5	49	69.2	91.7	108	142	179	210	296	1.35
	5.4	6.1	7.5	9.5	11.6	13.6	18	22	26	28	32	35	39	46	1.50
3	6.9	11	14.3	20.4	25	36	54	79	101	120	156	197	232	324	1.32
	6.2	7.2	8.5	10.9	14	16	20.3	25	30	32.2	37.2	40.3	45	54	1.48
4	7.5	12	15.6	22.2	30.1	39	59	83	110	131	170	215	254	353	1.29
	6.8	8.8	9.5	12.3	16.3	18.4	22.5	28	33.4	36.8	42.3	45.7	50.5	60.7	1.45
5	8.2	13	17	24	32.6	42.3	63.4	70	119	142	185	233	275	382	1.28
	7.3	8.9	10.5	13.2	17.2	19.8	24.3	30.4	36.3	39.9	45.6	49.2	54.7	65.8	1.43
6	8.5	13.4	17.6	24.9	33.8	43.3	65.7	93.4	124	147	198	242	285	396	1.27
	7.8	9.5	11.4	14.1	18.1	21.2	26.2	32.8	39.2	43	48.9	52.6	58.9	70.9	1.42
7	8.7	13.8	18.1	25.7	35	45.3	68	96.8	128	151	198	250	294	410	1.26
	8.2	10.2	12.3	15	19	22.5	28	35	42	46	52	56	63	76	1.41
8	9.1	14.4	18.9	26.9	36.6	47.4	71	100.8	134	158	207	261	307	428	1.25
	8.7	10.7	13.5	16	20	24	30	37	44	49	57	61	68	82	1.4
9	9.5	15.1	19.7	28.1	38.1	49.4	74	105	139	164	216	272	320	436	1.24
	9.3	11.3	14.1	16.5	20.6	24.5	31.5	39	46.5	51.5	60	64	72	88	1.39
10	9.9	15.7	20.4	29.2	39.6	51.3	77	109	144	171	224	282	332	463	1.24
	9.8	11.9	14.6	16.9	21.3	25	33	41	49	54	62	67	75	90	1.38
12	10.4	16.5	21.6	30.7	41.7	54.1	81.1	115	152	180	236	298	350	488	1.23
	10.9	13	15.7	17.7	22.5	26	36	45	53	59	67	73	81	97	1.38
14	10.9	17.2	22.6	32.1	43.5	56.5	85.2	120	160	189	247	311	366	510	1.22
	11.6	13.9	17.0	20.4	25.5	30	39	49	58	64	73	79	93	106	1.37
16	11.7	18.5	24.3	34.5	46.7	60.6	91.4	128	172	203	265	334	393	548	1.21
	12.0	14.8	18.2	23	28.5	34	42	52	62	68	78	85	95	114	1.36
18	16.5	23.2	31.0	44.8	61.9	83.7	127	187	355	305	393	492	596	708	1.21
	14.5	15.9	19.4	24.0	29.8	35.5	44	55	66	72	82	90	100	120	1.36
20	17.0	26.1	35.0	51.0	71.0	97.3	148	220	302	362	465	582	712	806	1.2
	13.6	17.0	20.5	25.0	31.0	37	46	58	69	76	86	94	105	125	1.35
25	18.7	28.8	38.6	56.3	78.3	107.2	164	243	333	400	533	642	786	978	1.19
	15.3	19.1	22.9	28.3	35.0	42	52	66	78	86	97	106	119	141	1.34
30	20.5	31.5	41.2	61.5	85.5	117.1	179	265	364	437	571	702	859	1150	1.18
	17.0	21.1	25.2	31.4	39.0	47	51	73	87	96	108	118	132	157	1.33
40	22.3	34.1	45.7	66.7	92.7	127	194	287	395	473	608	762	932	1322	1.16
	20.4	25.2	30.0	37.5	46.4	56	70.2	87.3	104	114	130	142	158	189	1.31
50	24.4	37.3	50.0	73	101	139	212	314	432	518	665	834	1020	1450	1.15
	23.5	28.6	34.4	43.7	54.0	65.0	82.0	102	121	133	151	165	184	220	1.29
60	26.5	40.5	54.3	79.3	135	181	305	445	626	752	960	1218	1480	2140	1.15
	26.5	32.0	38.7	49.9	61.9	73.5	95	119	140	155	177	199	222	265	1.28
70	28.7	43.7	58.6	85.6	156	208	346	510	717	861	1100	1396	1694	2455	1.147
	29.4	35.4	43	55.9	69	82	106	133	157	173	198	222	248	296	1.27
80	32.0	48.7	65.2	95.2	172	232	386	568	800	960	1220	1550	1890	2730	1.14
	34.3	42.3	51.1	66.1	81	97	126	156	187	205	234	263	293	350	1.26
90	33.7	51.4	68.8	100.4	181	245	407	598	842	1011	1288	1635	1990	2880	1.14
	37.9	46.1	55.9	71.9	88.5	106	134	171	204	224	256	287	320	284	1.26
100	35.4	54.0	72.3	105.5	190	256.5	427	628	884	1062	1355	1720	2690	3030	1.135
	41.1	49.8	60.7	77.7	96	114	149	186	220	242	277	311	347	416	1.25
120	42.1	64.3	86.0	125.6	227	305	508	748	1052	1265	1610	2050	2490	3600	1.128
	52.2	63.4	77.0	98.9	122	145	189	236	280	308	352	395	440	527	1.22

( ) 1. 가 -18  
2.