

A.8.1 / -

	°C	kg/m ³	kcal/kg °C	kcal/m h °C
	20	2,710	0.214	196
95-96Al,3-5Cu,0.5 Mg	20	2,790	0.211	141
	20	11,370	0.031	30
	20	7,900	0.108	62.5
(C 4%)	20	7,270	0.1	45
(C<1.5%)				
0.5C	20	7,830	0.111	46
1.0C	20	7,800	0.113	37
1.5C	20	7,750	0.116	31
20Ni	20	7,990	0.11	16
2Cr	20	7,870	0.11	45
80Ni,15Cr	20	8,520	0.11	15
2Mn	20	7,870	0.11	33
	20	8,960	0.0915	332
75Cu, 25Sn	20	8,670	0.082	22
70Cu,30Zn	20	8,520	0.092	95
60Cu,40 Ni	20	8,920	0.098	19
(99.9%)	20	8,910	0.1005	77
	20	10,530	0.0559	360
	20	19,350	0.0321	140
	20	7,140	0.0918	96
	20	7,310	0.0541	55
	20	19,290	0.0309	267
	0	21,450	0.0318	58
(90Pt,10Ir)	0	21,615		26.6
95Ni,2Al,2Mg,1Si	100	8,150		25.5
A 80Ni,20Cr	100	8,300	0.106	11.9
		18,700	0.0275	28.3