

B.7. (Safety Valve)

B.7.1 (KS B 6216. 1998)

- 1) (Safety valve) : 가 , (가)
가 가
- 2) (Lift safety valve) : 가 () 1/40 1/4
가 가
- 3) (Full bore safety valve) : 가
- 4) (Start to discharge pressure; start to leak pressure) : 가
() , 가
- 5) (Opening pressure; Popping pressure) : 가
(Popping) 가
- 6) (Set Pressure) :
- 7) (Closing Pressure ; Reseating Pressure) : 가
, , 가 가
- 8) (Blowdown) :
- 9) (Over Pressure) : 가
- 10) (Allowable Over Pressure) :
- 11) (Coefficient of discharge) :
- 12) (Certified coefficient of discharge) :
- 13) (Flow rating pressure) :
- 14) (Back Pressure) : 가 가 .
- 15) (Built-up back pressure) : 가 ,
- 16) (Super imposed back pressure) : 가
- 17) (Theoretical reliving capacity) :
가 1 가 가
- 18) (Certified capacity; Rated reliving capacity) :
x x 0.9
- 19) (Lift) :
- 20) (Rated Lift) :
- 21) (Seat Diameter) : 가
- 22) (Throat diameter; Bore diameter) :
가
- 23) (Throat Area; Bore Area) :
- 24) ((Seat flow area; Curtain area) :
- 25) (Effective discharge area) :