

SP200

electropneumatic smart positioner



spirax
/sarco

SP200

The new generation of non-contact smart positioners

SP200 positioner – smart, simple, low cost

The precise control of valve position is essential for the accurate and efficient control of industrial processes. Valve positioners provide the electropneumatic interface, guaranteeing fast and accurate control by eliminating hysteresis and the effects of differential pressure whilst optimising actuator selection.

Smart

The Spirax Sarco SP200 positioner is enhanced by the ability to customise the control action, set travel limits and monitor valve position. The embedded menu driven program, accessed via the integrated keypad, eliminates the need for additional or remote software. Data logging of valve performance will assist maintenance diagnostics whilst adaptive action helps to compensate for changes in supply air pressure and stem friction. Having travel switches and a 4-20 mA retransmission as standard it is easy to monitor the valve in operation.

Simple

All SP200 units are supplied with a universal mounting kit making them quick and easy to assemble. They operate on a non-mechanical magnetic feedback system which is very easy to set-up and will not suffer wear, vibration or dirt problems. A simple autostroke routine makes it extremely quick and easy to commission and the keypad provides trouble free navigation through the menu system. Manual operation is available at the touch of a button.



Low cost of ownership

Options which were previously offered at extra cost are now included as standard. The new digital technology which is used in the SP200 makes it very energy efficient, there are very few mechanical elements and the effects of wear are significantly reduced, all contributing to guaranteed long-term reliability and reduced lifecycle costs.


Proven technology

The SP200 loop powered smart positioner is a development of the very successful SP2 model, which is widely acknowledged to have set the industry standard for being one of the easiest positioners to commission.

Key features and benefits:

- All the user friendly features of the SP2 are retained In the SP200:
 - Autostroke.
 - Easy customisation of performance through menu driven embedded software.
 - Digital air control to minimise running costs.
 - Adaptive action to compensate for process variations.
 - Continuous data logging of valve performance.
- Utilises a non-contact hall effect magnetic feedback linkage. This detects changes in magnetic flux when the control stem moves, then feeds it back to the positioner so that it can regulate the air signal to the actuator.
- Larger, easier to read digital display and enhanced reliability due to the elimination of most mechanical elements.
- Travel switches and 4 – 20 mA retransmission as standard.

The SP200 digital display



Digital indication of % travel



On screen commissioning aids include input signal, software travel switch status and valve diagnostics



Embedded menu driven programmable software



The SP200 range

Product	Input signal range	Stroke range	Characteristic	Travel switch and 4 – 20 mA retransmission feature	Enclosure rating	Namur specification fixing kit	Gauge block with two 0 to 7 bar gauges
SP200	4 – 20 mA	10 to 100 mm	Equal %, fast opening, linear	Included	IP65	Included	Not included
SP200M	4 – 20 mA	10 to 100 mm	Equal %, fast opening, linear	Included	IP65	Included	Included

Electropneumatic smart positioner

SP200



Electropneumatic smart positioner with gauge block

SP200M



Key features and benefits

Key feature	Key reason	Key benefit	
	Quick and simple to commission	Autostroke commissioning feature	Reduces time and cost
	Significant reduction in time and complexity to install. Unaffected by vibration, dirt or susceptible to wear.	Hall effect magnetic valve position sensing, no mechanical feedback linkage	Reduces time and cost to commission, improved reliability and accuracy
	Energy efficient	Digital air control, near zero air consumption at controlled position	Low running costs
	Programmable functions via integral keypad	Easy and quick to commission, easy optimisation of valve performance	Control application optimised to application requirement
	Easy local monitoring of valve/actuator/positioner	Large digital display and on screen commissioning which includes valve position, travel switch mode, input signal status and diagnostics	Enhanced process control information for the user
	Even more features as standard	Travel switches and 4 – 20 mA retransmission features included as standard	Simpler selection, greater flexibility, better value for money
	Easy monitoring of air signals allows easy set up and diagnostics	Manifold and gauges available on SP200M	Quick to commission, easy to monitor air supply
	One model suits most positioner applications	Compatible with many pneumatic actuator types	Commonality of equipment, reduced supplier base
	Part of a total control solution from Spirax Sarco	One of many controls and implementation solutions which may be acquired separately or as a complete one-stop-shop controls solution	Peace of mind that your purchases are supported wherever you are in the world and that one single contact will fulfil your controls requirements from design to after sales service

Group companies

Africa

South Africa

Americas

Argentina
Brazil
Canada
Mexico
USA

Asia

China
India
Japan
Korea
Malaysia
Singapore
Taiwan
Thailand

Australasia

Australia
New Zealand

Europe

Austria
Belgium
Czech Republic
Denmark
Finland
France
Germany
Italy
Norway
Poland
Portugal
Russia
Slovak Republic
Spain
Sweden
Switzerland
UK

Sales offices

Africa

Egypt
Kenya
Nigeria

Americas

Colombia
Venezuela

Asia

Hong Kong
Indonesia
Pakistan
Philippines
Vietnam

Europe

Austria
Hungary
Ireland

Middle East

UAE

Distributors

Africa

Algeria
Cameroon
Ethiopia
Ghana
Ivory Coast
Libya
Malawi
Mauritius
Morocco
Namibia
Senegal
Sudan
Tanzania
Tunisia
Uganda
Zambia
Zimbabwe

Americas

Bolivia
Chile
Colombia
Costa Rica
Dominican Republic
Ecuador
El Salvador
Guatemala
Honduras
Jamaica
Nicaragua
Panama
Paraguay
Peru
Trinidad and Tobago
Uruguay
Venezuela

Asia

Bangladesh

Australasia

Fiji

Europe

Bulgaria
Croatia
Cyprus
Estonia
Greece
Iceland
Latvia
Lithuania
Malta
Netherlands
Romania
Slovenia
Turkey

Middle East

Bahrain
Iran
Jordan
Kuwait
Lebanon
Oman
Qatar
Saudi Arabia
Syria



Some products, services or solutions may not be available in certain markets

Spirax-Sarco Limited
Cheltenham UK
GL53 8ER
t: +44 (0)1242 521361
f: +44 (0)1242 573342
e: controls@SpiraxSarco.com
www.SpiraxSarco.com/controls

spirax
/sarco