



Cert. No. LRQ 0963008

ISO 9001

## 'C' Series Valve Spares

### Spare parts



The spare parts available for the CE43, CE63 and CE83 valves, 1" to 8" (DN25 to DN200), are detailed below. No other parts are supplied as spares.

#### Available spares

|  |                      |           |
|--|----------------------|-----------|
| Actuator clamping nut                            |                      | <b>A</b>  |
| Gland seal kit                                   | PTFE seal set        | <b>B</b>  |
|  | Graphite packing set | <b>C</b>  |
| Valve plug                                       |                      | <b>D</b>  |
| Valve stem                                       |                      | <b>E</b>  |
| Valve gasket kit                                 | Graphite gasket      | <b>F1</b> |
|  | Bonnet Spacer        | <b>F2</b> |
|  | Spiral wound gasket  | <b>F3</b> |
| Valve seat                                       |                      | <b>F4</b> |
|  | Adaptor gasket       | <b>F5</b> |
| Piston seal kit                                  | Graphite             | <b>G</b>  |
|  | PTFE                 | <b>H</b>  |
| Valve seat                                       |                      | <b>I</b>  |
| Valve cage                                       |                      | <b>J</b>  |
| Reduction kit (seat, cage and reduction adaptor) |                      | <b>K</b>  |

**Note:** A 'valve gasket kit' should be ordered with the above items.

#### 'C' series valve



### Note:

When placing an order for spares please indicate clearly the model number, serial number and date code (found on the label of the valve body) to ensure that the order is processed quickly, efficiently and correctly.

### How to order spares

Always order spares by using the description given in the column headed 'Available spares'. Also state the information shown in the 'C' series valve selection guide, the serial number, and date code of the valve.

### 'C' series valve selection guide

|                      |  |                 |
|----------------------|--|-----------------|
| Valve size           | 1", 1½", 2", 2½", 3", 4", 5", 6" and 8"<br>DN25, 40, 50, 65, 80, 100, 125, 150 and 200 | <b>2"</b>       |
| Valve series         | C = Cage trim  | <b>C</b>        |
| Valve characteristic | E = Equal percentage   | <b>E</b>        |
|                      | F = Fast opening   |                 |
|                      | L = Linear   |                 |
|                      | M = Modified equal percentage  |                 |
| Body material        | 4 = Carbon steel   | <b>4</b>        |
|                      | 6 = Stainless steel  |                 |
|                      | 8 = Alloy steel  |                 |
| Connections          | 2 = Butt weld (2" to 8")   | <b>3</b>        |
|                      | 3 = Flanged  |                 |
|                      | 4 = Socket weld (1", 1½" and 2")   |                 |
| Stem sealing options | P = PTFE chevron   | <b>P</b>        |
|                      | H = Graphite   |                 |
|                      | B = Bellows  |                 |
| Seating options      | T = AISI 431 hardened  | <b>T</b>        |
|                      | G = PTFE soft seat   |                 |
|                      | W = Hard faced stellite AISI 316   |                 |
| Type of trim         | C = Standard cage  | <b>C</b>        |
|                      | P = Noise reducing perforated cage   |                 |
|                      | A = Anti-cavitation cage   |                 |
| Number of stages     | 1 = One  | <b>1</b>        |
|                      | 2 = Two  |                 |
|                      | 3 = Three  |                 |
|                      | Other = To be specified  |                 |
| Trim balancing       | B = Balanced   | <b>U</b>        |
|                      | U = Unbalanced   |                 |
| Bonnet type          | S = Standard   | <b>S</b>        |
|                      | H = Extended for high temperature  |                 |
|                      | L = Extended for low temperature   |                 |
| Reduced trim         | 0 = No Reduction   | <b>1</b>        |
|                      | 1 = 1 Reduction  |                 |
|                      | 2 = 2 Reductions   |                 |
|                      | 3 = 3 Reductions   |                 |
| Cv                   | To be specified  | <b>Cv 35</b>    |
| Connection type      | To be specified  | <b>ANSI 300</b> |

**2" C E 4 3 P T C 1 U S 1 Cv 35 ANSI 300**

### How to order example

1 - Valve seat and valve gasket kit for a 2" CE43PTC1US1 Cv35 valve, flanged to ANSI 300, serial number FR00001. Date coded M00.

### How to fit spares

Full instructions are given in the Installation and Maintenance Instructions supplied with the spare.

