

A.6.1

(m/s)	(m ³ /h)											
	15mm	20mm	25mm	32mm	40mm	50mm	65mm	80mm	100mm	125mm	150mm	200mm
3.0	2	4	6	11	15	23	39	54	93	141	202	355
3.5	3	5	7	13	17	27	46	63	108	165	236	414
4.0	3	5	8	14	19	31	53	72	123	188	270	472
4.5	3	6	9	16	22	35	59	81	139	212	303	529
5.0	4	6	10	18	24	39	66	90	154	235	337	590
5.5	4	7	11	20	27	43	72	99	170	259	371	652
6.0	4	8	12	22	29	47	78	108	185	283	403	709
6.5	5	8	13	23	32	51	85	117	200	306	439	767
7.0	5	9	14	25	34	54	92	126	216	329	472	828
7.5	5	10	15	27	36	58	98	135	231	353	504	886
8.0	6	10	16	29	39	62	105	144	247	378	540	947
8.5	6	11	17	31	41	66	112	153	262	400	572	1001
9.0	6	12	18	32	44	70	118	162	278	425	608	1066

()