

CS10

stainless steel
clean steam separator

A solution to ensure steam dryness

The CS10 is a unique design from Spirax Sarco which has been developed to overcome the related problems associated with wet steam, including control valve damage and failure to comply to steam sterilisation standards EN 285 and HTM 2010.

Key features

- Designed to exceed the steam dryness value of 0.95 as per standards EN 285 and HTM 2010.
- Unique, patent pending design with removable baffle plate design to facilitate periodic de-rousing and inspection.
- Designed in accordance with the ASME BPE guide (2005 edition) for the Biopharmaceutical industry.
- Fully traceable 316L stainless steel material throughout to ensure system integrity.
- All elastomers compliant to FDA regulation CFR 21, part 177, section 2600. USP class VI elastomers are only available in ½", ¾" and 1" sizes.
- CS10-1 is available with 0.5 µm Ra maximum as standard.
- Part of a dedicated high purity product range from Spirax Sarco.



Sanitary
control valve



Sanitary ball valves




Sanitary steam trap

The range and options

Type	Size	Surface finish	Welds	Connections	Options
CS10 - 1	½" - 2"	0.5 µm Ra	Ground smooth and polished	Sanitary clamp or Tube weld ends	Electropolishing
CS10 - 2	½" - 2"	0.75 µm Ra	Left as laid	Sanitary clamp or Tube weld ends	-

Typical application



Spirax-Sarco Limited
 Cheltenham UK
 GL53 8ER
 t: +44 (0)1242 521361
 f: +44 (0)1242 573342
 e: enquiries@SpiraxSarco.com
 www.SpiraxSarco.com

