



Cert. No. LRQ 0963008

ISO 9001

spirax sarco

TI-P257-01
 CH Issue 6

SV405, SV405X and SV406 Safety Valves

Description

The SV405, SV405X and SV406 are full nozzle safety valves for steam and air service in non-critical industrial processes requiring low flow, low pressure and temperature.

Available types

The SV405 and SV406 are available with a brass or stainless steel body, stainless steel nozzle and Viton 'O' ring seat seal as standard.

The SV405X has an austenitic stainless steel nozzle for applications where enhanced corrosion resistance is required.

Applications

The SV405 and the SV406 are designed to protect against overpressure in general process applications such as sterilisers, small compressors and pressure vessels.

Standards and approvals

Seat tightness complies with API standard 527.

This product fully complies with the requirements of the European Pressure Equipment Directive 97/23/EC and carries the **CE** mark.

Certification

The product is available with a manufacturers Typical Test Report.


Note: All certification / inspection requirements must be stated at the time of order placement.

Sizes and pipe connections

Inlet Screwed 1/2" or 3/4" BSP taper male BS 21 R or NPT


Outlet Screwed 3/4" BSP parallel female BS 21 Rp or NPT

Pressure / temperature limits




Set pressure range	Maximum	10 bar g
	Minimum	1 bar g
Backpressure	Maximum	10% of set pressure
	Minimum	-20°C
Temperature	Viton seat	Maximum +200°C
	Overpressure	Steam 10%
Performance data		Gas 10%
	Blowdown limits	Steam, gas 10%
	Derated coefficient of discharge values	Steam, gas 0.78

Designed for a maximum cold hydraulic test pressure of 20 bar g



Materials

No.	Part	Material	SV405	SV405X	SV406
1	Nozzle	Stainless steel 1.4301	•		
		Stainless steel 1.4401		•	•
2	Body	Brass EN 121640 CW617N	•		
		Stainless steel 1.4409		•	•
3	Screw	Stainless steel, A4	•	•	•
4	Cap	Brass EN 121640 CW617N	•	•	
		Brass EN 121640 CW617N, ELNP			•
5	Gasket	PTFE	•	•	•
6	Stem/disc holder	Stainless steel, X20 Cr Ni 17	•	•	•
7	O'ring	Viton, FPM 75	•	•	•
10	Spring plate	Stainless steel, ASTM A276 304	•	•	•
13	Adjusting screw	Stainless steel, ASTM A276 304	•	•	•
15	Spring	Stainless steel, 1.4310	•	•	•
17	Lever	Stainless steel, 304	•	•	•
29	Joint	Brass EN 121640 CW617N	•	•	
		Brass EN 121640 CW617N, ELNP			•



Dimensions, orifice, lift and weight
(approximate) in mm and kg

A	B	C	D	Orifice	Lift	Weight
37	50.7	137.7	152.7	8	3	0.75

Sizing

For the majority of applications, the valve capacity can be selected from the flow capacity table below, alternatively it can be sized using the online safety valve sizing and selection software at <http://www.spiraxsarco.com/prs/product-sizing.asp>

Flow capacity (in accordance with EN ISO 4126)

Saturated steam and air with 10% overpressure

Set pressure bar g	Dry saturated steam kg/h	Air (0°C @ 1013 mbar) Nm ³ /h
1.0	42	61
1.5	53	75
2.0	63	88
2.5	74	103
3.0	84	119
3.5	95	134
4.0	105	149
4.5	115	164
5.0	126	179
5.5	136	194
6.0	146	209
6.5	156	224
7.0	167	239
7.5	177	255
8.0	187	270
8.5	197	285
9.0	208	300
9.5	218	315
10.0	228	330

Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-P257-02) supplied with the product.

Installation note: The SV405 should always be installed with the centre line of the spring housing vertically above the valve.

How to order

Example: 1 off Spirax Sarco SV405 safety valve having 3/4" BSP inlet x 3/4" BSP outlet connections, with a set pressure of 5 bar.