



ANSI B 16,5'e göre flanş ölçüleri

- DN = anma çapı
A = flanş çapı
D2 = fatura çapı
D1 = delik eksen çapı
n = delik sayısı
d = delik çapı

DN		125/150 lbs		300 lbs		600 lbs		DN		125/150 lbs		300 lbs		600 lbs	
		inch	mm	inch	mm	inch	mm			inch	mm	inch	mm	inch	mm
1/2"	A	3 1/2	88.9	3 3/4	95.2	3 3/4	95.2	3"	A	7 1/2	190.5	8 1/4	209.6	8 1/4	209.6
	b	7/16	11.1	9/16	14.3	9/16	14.3		b	15/16	23.8	1 1/8	28.6	1 1/4	31.8
	D ₂	1 3/8	34.9	1 3/8	34.9	1 3/8	34.9		D ₂	5	127	5	127	5	127
	D ₁	2 3/8	60.3	2 5/8	66.7	2 5/8	66.7		D ₁	6	152.4	6 5/8	168.3	6 5/8	168.3
	n	4	4	4	4	4	4		n	4	4	8	8	8	8
	d	5/8	15.9	5/8	15.9	5/8	15.9		d	3/4	19	7/8	22.2	5/8	15.9
3/4"	A	3 7/8	98.4	4 5/8	117.5	4 5/8	117.5	3 1/2"	A	8 1/2	215.9	9	228.6	9	228.6
	b	1/2	12.7	5/8	15.9	5/8	15.9		b	15/16	23.8	1 3/16	30.2	1 3/8	34.9
	D ₂	1 11/16	42.9	1 11/16	42.9	1 11/16	42.9		D ₂	5 1/2	139.7	5 1/2	139.7	5 1/2	139.7
	D ₁	2 3/4	69.8	3 1/4	82.5	3 1/4	82.5		D ₁	7	177.8	7 1/4	184.2	7 1/4	184.2
	n	4	4	4	4	4	4		n	8	8	8	8	8	8
	d	5/8	15.9	3/4	19	3/4	19		d	3/4	19	7/8	22.2	1	25.4
1"	A	4 1/4	108	4 7/8	123.8	4 7/8	123.8	4"	A	9	228.6	10	254	10 3/4	273
	b	9/16	14.3	1 1/16	17.5	1 1/16	17.5		b	15/16	23.8	1 1/4	31.7	1 1/2	38.1
	D ₂	2	50.8	2	50.8	2	50.8		D ₂	6 3/16	157.2	6 3/16	157.2	6 3/16	157.2
	D ₁	3 1/8	79.4	3 1/2	88.9	3 1/2	88.9		D ₁	7 1/2	190	7 7/8	200	8 1/2	215.9
	n	4	4	4	4	4	4		n	8	8	8	8	8	8
	d	5/8	15.9	3/4	19	3/4	19		d	3/4	19	7/8	22.2	1	25.4
1 1/4"	A	4 5/8	117.5	5 1/4	133.4	5 1/4	133.4	5"	A	10	254	11	279.4	13	330.2
	b	5/8	15.9	3/4	19	13/16	20.6		b	15/16	23.8	1 3/8	34.9	1 3/4	44.4
	D ₂	2 1/2	63.5	2 1/2	63.5	2 1/2	63.5		D ₂	7 5/16	185.7	7 5/16	185.7	7 5/16	185.7
	D ₁	3 1/2	88.9	3 7/8	98.4	3 7/8	98.4		D ₁	8 1/2	215.9	9 1/4	234.9	10 1/2	266.7
	n	4	4	4	4	4	4		n	8	8	8	8	8	8
	d	5/8	15.9	3/4	19	3/4	19		d	7/8	22.2	7/8	22.2	1 1/8	28.6
1 1/2"	A	5	127	6 1/8	155.6	6 1/8	155.6	6"	A	11	279	12 1/2	317.5	14	355.6
	b	1 1/16	17.5	1 3/16	20.6	7/8	22.2		b	1	25.4	1 7/16	36.5	1 7/8	47.6
	D ₂	2 7/8	73	2 7/8	73	2 7/8	73		D ₂	8 1/2	216	8 1/2	215.9	8 1/2	215.9
	D ₁	3 7/8	98.4	4 1/2	114	4 1/2	114		D ₁	9 1/2	241	10 5/8	269.9	11 1/2	292.1
	n	4	4	4	4	4	4		n	8	8	12	12	12	12
	d	5/8	15.9	7/8	22.2	7/8	22.2		d	7/8	22.2	7/8	22.2	1 1/8	28.6
2"	A	6	152.4	6 1/2	165.1	6 1/2	165.1	8"	A	13 1/2	342.9	15	381	16 1/2	419
	b	3/4	19	7/8	22.2	1	25.4		b	1 1/8	28.6	1 5/8	41.3	1 3/4	44.4
	D ₂	3 5/8	92.1	3 5/8	92.1	3 5/8	92.1		D ₂	10 5/8	269.9	10 5/8	269.9	10 5/8	269.9
	D ₁	4 3/4	121	5	127	5	127		D ₁	11 3/4	298.4	13	330.2	13 3/4	349.2
	n	4	4	8	8	8	8		n	8	8	12	12	12	12
	d	3/4	19	3/4	19	3/4	19		d	7/8	22.2	1	25.4	1 1/4	31.8
2 1/2"	A	7	177.8	7 1/2	190.5	7 1/2	190.5	10"	A	16	406.4	17 1/2	444.5	20	508
	b	7/8	22.2	1	25.4	1 1/8	28.6		b	1 3/16	30.2	1 7/8	47.6	2 1/2	63.5
	D ₂	4 1/8	104.8	4 1/8	104.8	4 1/8	104.8		D ₂	12 3/4	323.8	12 3/4	323.8	12 3/4	323.8
	D ₁	5 1/2	139.7	5 7/8	149.2	5 7/8	149.2		D ₁	14 1/4	361.9	15 1/4	387.4	17	431.8
	n	4	4	8	8	8	8		n	12	12	16	16	16	16
	d	3/4	19	7/8	22.2	7/8	22.2		d	1	25.4	1 1/8	28.6	1 3/8	34.9