



**SLOWER CYCLING
MORE THERMALLY EFFICIENT
LONGER LASTING**

Redesigned...to make the **TD** line even more efficient than ever before! Here's the trap acclaimed for its zero steam loss— now cycling slower and discharging condensate slightly cooler than its predecessors. How? Our space age ceramic technology slows control chamber cooling. The result—longer life and higher thermal efficiency.

- Durable stainless body, disc and cap
- Electroless Nickel plated bodies
- Outstanding 5 year warranty for 300 psig or less steam pressure
- No operational steam loss
- Saturated or superheated steam
- Discharges close to saturation
- Hardened stainless steel disc and seats assures positive seating
- Tight shut-off
- On-off operation easy to test
- Cleanable
- Horizontal or vertical installation
- Wide range of capacities
- Improve efficiency on steam main drip, steam tracing and as a process trap on constant pressure type applications



Cool Blue TD52™

Pressure Range:

3.5 to 600 psig

Standard Connections:

3/8", 1/2", 3/4", 1" NPT

Universal Connections (UTD)

1/2", 3/4", 1" NPT, SW for all standard swivel connectors

UTD Connector Options:

Straight, strainer, strainer with BDV, strainer with in-trap sensing; stainless or carbon steel; left- or right-hand connectors

