


spirax sarco

Safety Valves SV74 Series

The **SV74** Series valves are built in conformance to Section I and VIII of the ASME boiler and pressure vessel code. They are primarily intended for use on power boilers and unfired pressure vessels where ASME Section I or VIII stamped valves are required. The orifice areas listed are actual orifice areas and should not be confused with the API effective orifice areas shown in most safety valve catalogs.

Model	SV74	
Sizes	1-1/2" x 2" to 6" x 8"	
Connections	Inlet: ANSI 300 RF	Outlet: ANSI 150 RF
Construction	Cast Steel body with Stainless Steel Trim	
Options	Tungsten Spring Drip pan elbow-See TI-3-2141-US	



Construction Materials


No.	Part	Material	
1	Body	ASME SA 216 Gr. WCB	
2	Seat	F to H orifice	ASTM A479 304
		J to R orifice	ASTM A351 Grade CF8
3	Bonnet	ASME SA 216 Gr. WCB	
4	Cap	ASTM A126 Class B	
5	Disc	F to H orifice	ASTM A479 304
		J to R orifice	ASTM A217 CA15
6	Spring	Chrome-vanadium alloy steel or tungsten alloy steel	
7	Upper adjusting ring	ASTM A351 Grade CF8	
8	Lower adjusting ring	ASTM A351 Grade CF8	
9	Stem (lower)	ASTM A479 Type 410	
10	Stem (upper)	ASTM A479 Type 410	
11	Spring washers (2 off)	ASTM A105	
12	Bonnet stud	ASTM A193 Grade B7	
13	Bonnet nut	ASTM A194 Grade 2H	
14	Adjusting screw	ASTM A479 Type 410	
15	Adjusting screw nut	Carbon steel	
16	Release ring	Carbon steel	
17	Lock-nuts (2 off)	Carbon steel	
18	Lever	Grey iron	
20	Cap set screw	Carbon steel	
21	Upper adjusting ring pin	Stainless steel	
22	Lower adjusting ring pin	Stainless steel	
23	Disc ball	Stainless steel	
24	Pin washer	Carbon steel	
25	Lever pin	Carbon steel	
26	Lock-nut	Carbon steel	
27	Guide plate	Carbon steel	
40	Stem pin	Carbon steel	
41	Name plate	Stainless steel	

Limiting Operating Conditions (Steam)

Max. Operating Pressure (PMO)	300 psig (20.7 barg)
Max. Operating Temperature	422°F (217°C)
	750°F (399°C) with Tungsten Spring

See **TI-3-2121-US** for sizing data.

Pressure/Temperature Limits



- The product **must not** be used in this region.
- A tungsten alloy spring must be used in this region.
- Consult Spirax Sarco for further information


Typical Applications

Protection of steam system downstream of pressure regulating stations, on inlet to such equipment as air coils, heat exchangers and process vessels. Also for use on flash recovery vessels on condensate return systems to protect vessels. Air systems to protect accumulation vessels and air equipment from over-pressurization. Steam boilers and generators.

*Local regulation may restrict the use of this product below the conditions quoted. Limiting conditions refer to standard connections only.
In the interests of development and improvement of the product, we reserve the right to change the specification.*

TI-3-216-US 06.11

Safety Valves SV74 Series



Dimensions, weights and orifice sizes (approximate) in inches and lbs

Valve inlet Size	Valve inlet Connection	Valve outlet Size	Valve outlet Connection	Orifice letter	A ins	B ins	C ins	Weight lbs
1½"	ANSI 300	2"	ANSI 150	F	4.25	4.5	15.7	31
1½"	ANSI 300	2"	ANSI 150	G	4.25	4.5	15.7	31
1½"	ANSI 300	2½"	ANSI 150	H	4.90	4.8	16.2	46
1½"	ANSI 300	2½"	ANSI 150	J	4.90	4.8	16.2	46
2"	ANSI 300	3"	ANSI 150	K	5.60	5.1	18.5	62
2½"	ANSI 300	4"	ANSI 150	L	6.40	6.1	20.1	90
3"	ANSI 300	4"	ANSI 150	M	6.50	6.5	25.0	117
4"	ANSI 300	6"	ANSI 150	N	7.50	7.2	26.7	198
4"	ANSI 300	6"	ANSI 150	P	8.30	7.1	28.7	212
6"	ANSI 300	8"	ANSI 150	Q	9.40	9.9	34.8	384
6"	ANSI 300	8"	ANSI 150	R	10.00	10.9	43.9	633

SV7 safety valve selection guide

Series number	SV7	SV7
Construction	4 = Cast steel	4
ASME section	V = ASME Code Section I U = ASME Code Section VIII Blank = Valve without code stamp	V
Size and connection	S = 1½" ANSI 300 x 2" ANSI 150 T = 1½" ANSI 300 x 2½" ANSI 150 U = 2" ANSI 300 x 3" ANSI 150 V = 2½" ANSI 300 x 4" ANSI 150 W = 3" ANSI 300 x 4" ANSI 150 X = 4" ANSI 300 x 6" ANSI 150 Y = 6" ANSI 300 x 8" ANSI 150	X
Actual orifice area Sq. In.	F = 0.328 G = 0.537 H = 0.841 J = 1.374 K = 1.968 L = 3.054 M = 3.846 N = 4.633 P = 6.830 Q = 11.811 R = 17.123	P
Set pressure	Specify set pressure from 5 psi g to 250 psi g	180

For tungsten alloy spring add 'T' after set pressure eg: 180 'T'.

SV7	4	-	V	-	X	P	-	180
------------	----------	---	----------	---	----------	----------	---	------------

How to order

Example 1: 1 off Spirax Sarco SV74-V-XP-180 safety valve having a set pressure of 180 psi g.

If a tungsten alloy spring was required the order would read as follows:
Example 2: 1 off Spirax Sarco SV74-V-XP-180T safety valve having a set pressure of 180 psi g.

Installation

Safety valves must be installed in a vertical upright position and drained via connection 19.

Avoid having the operating pressure too near the safety valve set pressure. A very minimum differential of 5 psig or 10% (whichever is greater) is recommended. An even greater differential is desirable, when possible, to assure better seat tightness and valve longevity.

Avoid discharge piping where its weight is carried by the safety valve. Even though supported separately, changes in temperature alone can cause piping strain. We recommend that drip pan elbows or flexible connections be used where possible. If required, remove protective plug (19) and route to drain.

For full details on proper installation, please refer to the installation, operating and maintenance instructions, IM-S13-33.

Maintenance

Develop a regular program of visual inspection. Inspection should include checking for clogged drains, discharge pipe, and dirt build-up around the valve seat.

Test the safety valve every 6 months (depending on plant's age and condition) either by raising the system pressure to the valve's set pressure or operating the hand lever.

How to Specify

To simplify selection and specifying of Spirax Sarco safety valves, use the following type numbering system. The type numbering system is ideal as the digit which comprises a specific type number has a distinct significance. The digits describe the basic valve series, materials of construction, connection type, boiler code conformance, inlet and outlet connections, orifice size and set pressure.