

# USTS II

## Compact Universal Connection Steam Trap Station Now With Isolation Handle Option

**SMALLEST FACE TO FACE IN THE INDUSTRY  
THERMALLY EFFICIENT  
SIGNIFICANT REDUCTION IN INSTALLATION COST**

The Spirax Sarco USTS II series of steam trap stations have been designed to be a complete trap station in a very compact size. The trap station is comprised of two isolation valves for inlet and outlet flow, an inlet strainer blow down valve and an out test valve with mount for a universal style of steam trap. Blowdown valves can also be used for depressurization of station for trap maintenance.

- Works with all standard universal connection steam traps.
- Allows for trap change out in less than 5 minutes.
- Minimal heat loss.
- Easy operation.
- Robust construction.
- One ½" wrench operates blowdown valves.
- Saturated or Superheated Steam.
- Maintainable (can be cleaned).
- Horizontal installation.
- Wide pressure range 0 to 650 psig.
- For use with steam main drips, tracers, and small process flows.

**spirax**  
**sarco**



### USTS II Universal Steam Trap Station

All Stainless Construction

Sizes:

1/2", 3/4"

Connections

NPT, SW or NPT X SW

Left hand and Right hand configurations

Works with Thermo-Dynamic, Thermostatic, Inverted bucket, Float and Thermostatic and Bimetal steam trap types