

TI-P133-58 CMGT Issue 8

## Description

The M10Si ISO three-piece body ball valve has been designed for use as an isolating valve, not a control valve, has a lockable handle as standard and can be serviced without removal from the pipeline (screwed and welded versions only). It can be used for steam and other industrial fluids for services ranging from vacuum to the higher temperatures and pressures.



## **ISO** mounting

The integral ISO body mounting allows the valve to be automated without losing seal integrity, as the body does not require disassembly. Manual to remote control may therefore be easily accomplished by the ISO range of Spirax Sarco ball valves.

### Available types

M10Si2ISO	Zinc plated carbon steel body, PDR 0.8 seats.
M10Si3ISO	Stainless steel body, PDR 0.8 seats.
M10Si4ISO	Complete stainless steel, PDR 0.8 seats.

Note: The nomenclature will be followed with either FB (full bore) or RB (reduced bore).

### **Standards**

This product fully complies with the requirements of the Pressure Equipment Directive (PED) and carries the CE mark when so required.

### Certification

This product is available with certification to EN 10204 3.1. Note: All certification/inspection requirements must be stated at the time of order placement.

## **Technical data**

Flow characteristic	Modified linear
Port	Full and reduced bore versions
Leakage test procedure to ISC	0 5208 (Rate A)/EN 12266-1 (Rate A)
Antistatic device	Complies with ISO 7121 and BS 5351

### Sizes and pipe connections

Full bore Screwed and welded ¼", ¾", ½", ¾", 1", 1¼", 1½" and 2" BSP, BSPT, API/NPT, BW, SW	Flanged DN15 to DN50 ASME Class 150, ASME Class 300, and EN 1092 PN40.
Reduced bore Screwed and welded ¼", ¾", ½", ¾", 1", 1¼", 1½", 2" and 2½" BSP, BSPT, API/NPT, BW, SW	Flanged DN15 to DN65 ASME Class 150, ASME Class 300, and EN 1092 PN40.

# Pressure/temperature limits



The product **must not** be used in this region.

**A** - **B** 2" FB and 2<sup>1</sup>/<sub>2</sub>" RB only.

**A** - **C** <sup>1</sup>/<sub>4</sub>" - 1<sup>1</sup>/<sub>2</sub>" FB, RB and 2" RB.

Note: The flange standard may restrict the maximum operating pressure. Please check with Spirax Sarco.

PMA Maximum allowable pressure	100 bar g @ 60 °C
TMA Maximum allowable temperature	260 °C @ 0 bar g
Minimum allowable temperature	-29 °C
PMO Maximum operating pressure for saturated steam service	17.5 bar g
TMO Maximum operating temperature	260 °C @ 0 bar g
Minimum operating temperature Note: For lower operating temperatures consult Spirax Sarco	-29 °C
$\Delta PMX$ Maximum differential pressure is limited to the PMO	
Designed for a maximum cold hydraulic test pressure of	150 bar g

# **Materials**



No.	Part		Material	
		M10Si2 ISO	Zinc plated carbon steel	ASTM A105
1	Body	M10Si3 ISO M10Si4 ISO	Stainless steel	ASTM A 182 F 316L
		M10Si2 ISO	Zinc plated carbon steel	ASTM A105
2	Сар	M10Si3 ISO M10Si4 ISO	Stainless steel	ASTM A 182 F 316L
3	Ball		Stainless steel	AISI 316
4	Stem		Stainless steel	AISI 316
5	Seat		Carbon/graphite reinforced PTFE	PDR 0.8
6	Stem seal		Reinforced PTFE antistatic	
7	Separator	M10Si2 ISO M10Si3 ISO	Zinc plated carbon steel	SAE 1010
		M10Si4 ISO	Stainless steel	AISI 316
3	Spring washer		Stainless steel	AISI 301
Э	Nut	M10Si2 ISO M10Si3 ISO	Zinc plated carbon steel	SAE 1010
		M10Si4 ISO	Stainless steel	AISI 304
10	Name-plate (Not	shown)	Stainless steel	AISI 430
11	Stem nut	M10Si2 ISO M10Si3 ISO	Zinc plated carbon steel	SAE 1010
		M10Si4 ISO	Stainless steel	AISI 304
12	Lever	M10Si2 ISO M10Si3 ISO	Zinc plated carbon steel	SAE 1010
		M10Si4 ISO	Stainless steel	AISI 316

For parts 14 to 23 see page 4

# Materials (continued)



on steel Grade 5 AISI 304 on steel SAE 1010 AISI 304 AISI 316				
AISI 304 on steel SAE 1010 AISI 304				
on steel SAE 1010 AISI 304				
AISI 304				
AISI 216				
A131 310				
on steel SAE 12L 14				
AISI 304				
EPDM geothermal (Viton on request)				
AISI 316				
on steel SAE 1010				
AISI 316				
AISI 304L				
2				

# For parts 1 to 12 see page 3

### Dimensions (approximate) in mm Reduced bore

uu		•												
Size	Α	A1	A2	A3	A4	В	B1	С	C1	D	D1	D2	D3	E
1/4"	66	63	-	-	-	162	-	93	-	24	-	-	-	11
3⁄8"	66	63	-	-	-	162	-	93	-	24	-	-	-	11
1/2"	66	66	108	130	140	162	145	93	81	24	89	95	95	11
3/4"	72	60	117	150	152	162	145	95	84	26	98	105	117	14
1"	87	84	127	160	165	162	162	106	100	31	108	115	124	21
1¼"	104	94	140	180	178	162	162	106	104	37	118	140	133	25
1½"	110	102	165	200	190	186	185	116	112	41	127	150	155	31
2"	125	118	178	230	216	186	185	123	120	48	152	165	165	38
<b>2½</b> "	153	152	-	-	241	251	-	142	-	57	-	-	190	51
Full be	ore			Î								•		
Size	A	A1	A2	A3	A4	В	B1	С	C1	D	D1	D2	D3	E
1⁄4"	66	63	-	-	-	162	-	93	-	24	-	-	-	11
3/8"	66	63	-	-	-	162	-	93	-	24	-	-	-	11
1/2"	72	64	-	130	140	162	145	95	84	26	-	95	95	14
3/4"	87	84	-	150	152	162	162	101	100	31	-	105	117	21
1"	104	98	-	160	165	162	162	106	104	37	-	115	124	25
1¼"	110	106	-	180	178	186	185	116	112	41	-	140	133	31
11⁄2"	125	124	-	200	190	186	185	123	120	48	-	150	155	38
2"	153	152	-	230	216	251	250	142	140	57	-	165	165	51



- A: Scrd and BW
- A1: SW
- A2: Flanged ASME 150
- A3: Flanged PN40
- A4: Flanged ASME 300
- B: Scrd, BW, SW
- B1: Flanged ASME 150, PN40
- C: Scrd, BW, SW
- C1: Flanged ASME 150, PN40
- D: Scrd, BW, SW
- D1: Flanged ASME 150
- D2: Flanged PN40
- D3: Flanged ASME 300
- E: All versions

## Weights (approximate) in kg

0:		Reduced	l bore	Full bore				
Size	Scrd/BW/SW	PN40	ASME 150	ASME 300	Scrd/BW/SW	PN40	ASME 150	ASME 300
1/4"	0.65	-	-	-	0.65	-	-	-
3/8"	0.65	-	-	-	0.72	-	-	-
1/2"	0.72	2.30	1.77	1.70	0.95	2.60	1.87	2.40
3/4"	0.95	3.20	2.35	2.28	1.60	3.80	2.73	3.79
1"	1.60	4.20	3.47	2.91	2.05	4.70	3.55	5.01
1¼"	2.05	5.70	4.47	4.15	2.75	6.40	4.76	6.50
11⁄2"	2.75	6.80	5.96	5.88	4.25	8.30	5.82	9.22
2"	4.25	9.50	9.16	8.12	7.50	12.80	11.91	13.99
<b>2</b> ½"	7.50	-	-	15.85	-	-	-	-

# $\mathbf{K}_{\!_{\mathrm{v}}}$ values

Size	1⁄4"	<sup>3</sup> /8"	1⁄2"	3/4"	1"	11⁄4"	1½"	2"	<b>2½</b> "
Reduced bore	2.5	6.8	6	10	27	49	70	103	168
Full bore	2.5	6.8	17	36	58	89	153	205	-

For conversion:  $C_v (UK) = K_v \times 0.963$  $C_v (US) = K_v \times 1.156$ 

# Operating torque (N m)

Size	1⁄4"	3/8"	1/2"	3/4"	1"	1¼"	11/2"	2"	21/2"
Reduced bore	3.25	3.25	3.25	5.50	13.25	20	50	60	75
Full bore	3.25	3.25	5.50	13.25	20	50	60	75	-

The indicated torque values are for valves frequently operated, that are submitted to a maximum differential pressure of 40 bar. Valves that are subject to long static periods, may require greater break-out torque.

## Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions supplied with the product.

### How to order example:

1 off Spirax Sarco 1/2" screwed BSP M10Si2FB ISO ball valve.

### **Optional extras:**

- Self-venting ball.
- Extended stems 50 mm (2") and 100 mm (4") to allow full insulation.
- Fully degreased under request (i.e: Oxygen application).
- Viton O'rings (Part No 19) on request.

### **Spare parts**

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

