



MFP14-PPU (Vented) Automatic Pump Packaged Units

Description

The Spirax Sarco MFP14-PPU vented automatic pump packaged units are plug-in systems specifically designed to collect and pump hot condensate; commonly returned for use as boiler feedwater.

The MFP14-PPU is available with either single, duplex or triplex pumps, mounted on a single base plate, that can be used for duty only or duty/stand-by applications.

Operated by steam, the MFP14-PPU can be tailored to suit a wide range of condensate handling applications.

The standard pump is manufactured from SG iron, although cast steel and stainless steel versions are available on request.

Please note: Versions suitable for use with compressed air as the motive power and or other combinations are available as bespoke items. For further details contact your local Spirax Sarco office or representative.

Standards


The MFP14-PPU fully complies with the requirements of the Pressure Equipment Directive (PED).

Please note that all the welding is in accordance with the requirements of PED.

Certification

This product is available with a declaration of conformity. For other certification requirements contact Spirax Sarco.

Note: All certification/inspection requirements must be stated at the time of order placement. Retrospective certification/inspection may not be possible.



Single MFP14-PPU shown

Single MFP14-PPU	Sizes and pipe connections	Page 3
	Materials	Page 4
	Dimensions	Page 5
Duplex MFP14-PPU	Sizes and pipe connections	Page 6
	Materials	Page 7
	Dimensions	Page 8
Triplex MFP14-PPU	Sizes and pipe connections	Page 9
	Materials	Page 10
	Dimensions	Page 11

Approximate capacities

For full sizing details see pages 8 and 9

Unit size	Approximate maximum capacities (with 4 m lift) kg/h		
	Single MFP14-PPU	Duplex MFP14-PPU	Triplex MFP14-PPU
DN25 (1")	1 300		
DN40 (1½")	2 000	4 000	
DN50 (2")	4 000	8 000	
DN80 x DN50 (3" x 2")	6 000	12 000	18 000


Pressure/temperature limits

Body design condition		PN16
Maximum receiver operating pressure		0.5 bar g
Maximum motive inlet pressure (steam air or gas)	MFP14	13.8 bar g
	MFP14S	13.8 bar g
	MFP14SS	10.96 bar g
PMA Maximum allowable pressure	MFP14	16 bar g @ 120 °C
	MFP14S	16 bar g @ 120 °C
	MFP14SS	16 bar g @ 93 °C
TMA Maximum allowable temperature	MFP14	300 °C @ 12.8 bar g
	MFP14S	300 °C @ 10.8 bar g
	MFP14SS	300 °C @ 9.3 bar g
Minimum allowable temperature		0 °C
PMO Maximum operating pressure	MFP14	13.8 bar g @ 198 °C
	MFP14S	13.8 bar g @ 198 °C
	MFP14SS	10.96 bar g @ 188 °C
TMO Maximum operating temperature	MFP14	198 °C @ 13.8 bar g
	MFP14S	198 °C @ 13.8 bar g
	MFP14SS	188 °C @ 10.96 bar g
Minimum operating temperature		0 °C
Note: For lower operating temperatures consult Spirax Sarco		
Designed for a maximum cold hydraulic test pressure of		24 bar g

Single MFP14-PPU

Sizes and pipe connections

Unit size	Pipe connection	V (Condensate out)	W (Motive)	X (Overflow)	Y (Vent)	Z (Inlet)
DN25 (1")	PN16	DN25	DN15	DN50 PN16	DN100	DN40
	ASME 150	1" ASME 150	½" ASME 150	2" ASME 150	4" ASME 150	1½" ASME 150
DN40 (1½")	PN16	DN40	DN15	DN50 PN16	DN100	DN40
	ASME 150	1½" ASME 150	½" ASME 150	2" ASME 150	4" ASME 150	1½" ASME 150
DN50 (2")	PN16	DN50	DN15	DN50 PN16	DN150	DN65
	ASME 150	2" ASME 150	½" ASME 150	2" ASME 150	6" ASME 150	2½" ASME 150
DN80 x DN50 (3" x 2")	PN16	DN50	DN15	DN50 PN16	DN150	DN65
	ASME 150	2" ASME 150	½" ASME 150	2" ASME 150	6" ASME 150	2½" ASME 150




Single MFP14-PPU

Materials

No	Part	Material
1	Receiver	Mild steel
2	Base plate and frame	Mild steel
3	MFP14 pump	SG iron
4	DCV10 check valve	Stainless steel
5	BSA2T isolation valve	SG iron
6	Fig 37 strainer	SG iron
7	M10S2 RB ball valve straight handle	Carbon steel


No	Part	Material
8	PC10 Quick-fit connector	Stainless steel
9	UTD30L thermodynamic steam trap	Stainless steel
10	Steam inlet drain trap flexible hose	Mild steel/ stainless steel
11	Exhaust flexible hose	Mild steel/ stainless steel
12	Pipework	Mild steel



Single MFP14-PPU

Dimensions (approximate) in mm

Unit size	Dimensions (mm)																Q	R	
	A	B	C	D	E	F	G	H	J	K	L	M		N		O			P
												PN16	ASME 150	PN16	ASME 150				
DN25 (1")	1380	645	223	1081	499	225	1316	300	1119	600	300	1158	1138	987	965	220	1240	42	318
DN40 (1½")	1401	665	235	1081	499	225	1337	300	1139	600	300	1158	1139	1036	1015	220	1240	42	318
DN50 (2")	1606	775	259	1081	499	225	1541	300	1316	600	300	1274	1254	1270	1257	220	1240	42	318
DN80 x DN50 (3" x 2")	1716	775	259	1081	499	225	1650	300	1425	600	300	1274	1255	1269	1261	220	1240	42	318




Weight (approximate) in kg

DN25 (1")	DN40 (1½")	DN50 (2")	DN80 x DN50 (3" x 2")
230	255	285	325

Optional loop seal


A loop seal must be fitted to the overflow of the receiver. This can be purchased as an optional extra and must be specified at the time of order placement. Alternatively a loop seal can be created by the fitter at the point of installation.



Duplex MFP14-PPU

Sizes and pipe connections

Unit size	Pipe connection	V (Condensate out)	W (Motive)	X (Overflow)	Y (Vent)	Z (Inlet)
DN40 (1½")	PN16	DN40	DN15	DN50	DN150	DN50
	ASME 150	1½" ASME 150	½" ASME 150	2" ASME 150	6" ASME 150	2" ASME 150
DN50 (2")	PN16	DN50	DN15	DN50	DN200	DN65
	ASME 150	2" ASME 150	½" ASME 150	2" ASME 150	8" ASME 150	2½" ASME 150
DN80 x DN50 (3" x 2")	PN16	DN50	DN15	DN50	DN200	DN80
	ASME 150	2" ASME 150	½" ASME 150	2" ASME 150	8" ASME 150	3" ASME 150




Duplex MFP14-PPU

Materials

No	Part	Material
1	Receiver	Mild steel
2	Base plate and frame	Mild steel
3	MFP14 pump	SG iron
4	DCV10 check valve	Stainless steel
5	BSA2T Isolation valve	SG iron
6	Fig 37 strainer	SG iron
7	M10S2 RB ball valve with either oval or straight handle	Carbon steel



No	Part	Material
8	PC10 Quick-fit connector	Stainless steel
9	UTD30L thermodynamic steam trap	Stainless steel
10	Steam inlet flexible hose	Mild steel/stainless steel
11	Exhaust flexible hose	Mild steel/stainless steel
12	Pipework	Mild steel
13	DCV41 check valve	Stainless steel



Duplex MFP14-PPU

Dimensions (approximate) in mm

Unit size	Dimensions (mm)																	Q
	A	B	C	D	E	F	G	H	J	K	L	M		N		O	P	
												PN16	ASME 150	PN16	ASME 150			
DN40 (1½")	1 504	820	236	1944	700	350	1 454	425	1 213	850	191	1 816	N/A	1 416	N/A	285	1 496	328
DN50 (2")	1 654	921	259	1944	700	350	1 582	425	1 316	850	172	1 901	1 870	1 615	1 603	287	1 667	240
DN80 x DN50 (3" x 2")	1 822	921	259	1944	700	350	1 760	425	1 493	850	167	1 946	1 940	1 656	1 694	282	1 751	193




Weight (approximate) in kg

DN40 (1½")	DN50 (2")	DN80 x DN50 (3" x 2")
470	510	650

Optional loop seal


A loop seal must be fitted to the overflow of the receiver. This can be purchased as an optional extra and must be specified at the time of order placement. Alternatively a loop seal can be created by the fitter at the point of installation.



Triplex MFP14-PPU

Sizes and pipe connections

Unit size	Pipe connection	V (Condensate out)	W (Motive)	X (Overflow)	Y (Vent)	Z (Inlet)
DN80 x DN50 (3" x 2")	PN16	DN50	DN25	DN80	DN300	DN100
	ASME 150	2" ASME 150	1" ASME 150	3" ASME 150	12" ASME 150	4" ASME 150




Triplex MFP14-PPU

Materials

No	Part	Material
1	Receiver	Mild steel
2	Base plate and frame	Mild steel
3	MFP14 pump	SG iron
4	DCV10 check valve	Stainless steel
5	BSA2T isolation valve	SG iron
6	Fig 37 strainer	SG iron
7	M10S2 RB ball valve with either oval or straight handle	Carbon steel


No	Part	Material
8	PC10 quick-fit connector	Stainless steel
9	UTD30L thermodynamic steam trap	Stainless steel
10	Steam Inlet flexible hose	Mild steel/stainless steel
11	Exhaust flexible hose	Mild steel/stainless steel
12	Pipework	Mild steel
13	DCV41 check valve	Stainless steel



Triplex MFP14-PPU

Dimensions (approximate) in mm

Unit size	Dimensions (mm)																		
	A	B		C	D	E	F	G	H	J	K	L	M		N		O	P	Q
		PN16	ASME 150										PN16	ASME 150	PN16	ASME 150			
DN80 x DN50 (3" x 2")	1750	1181	1152	259	1686	760	350	1681	198	1378	1150	308	1111	1111	1224	1216	376	1725	535






Weight (approximate) in kg

1 050


Optional loop seal

A loop seal must be fitted to the overflow of the receiver. This can be purchased as an optional extra and must be specified at the time of order placement. Alternatively a loop seal can be created by the fitter at the point of installation.



How to size and select

Considering the inlet pressure, backpressure and filling head conditions, select the pump size which meets the capacity requirements of the application.



The known data

Condensate load **1500 kg/h**

Steam pressure available for operating pump **5.2 bar g**


Vertical lift from pump to the return piping **9.2 m**

Pressure in the return piping (piping friction negligible) **1.7 bar g**

Filling head on the pump available **0.3 m**

Note: It is strongly recommended that the maximum motive/backpressure differential is between 2-4 bar g.

How to use the sizing chart



Example
DN50 pump capacities

Selection example

Firstly calculate the total effective lift against which condensate must be pumped.

Total effective lift is calculated by adding **vertical lift from the pump to return piping (9.2 m)** to the **pressure in the return piping (1.7 bar g)**.

To convert pressure in the return pipe into pressure head, divide it by the conversion factor of 0.0981:-

$P_2 = 1.7 \text{ bar g} \div 0.0981 = 17.3 \text{ m Pressure head (lift)}$

The total effective lift then becomes calculable :-

$$9.2 \text{ m} + 17.3 \text{ m}$$

The total effective lift is 26.5 m

Now that the total effective lift has been calculated, a pump can be selected by plotting the known data onto the graphs on page 9.





1. Plot a horizontal line from 5.2 bar g (Motive pressure).
2. Plot a line indicating 26.5 m lift.
3. From the point where the motive pressure line crosses the m lift line, drop a vertical line to the X axis.
4. Read the corresponding capacity (2400 kg/h).

The capacity charts shown are for single pumps. The capacities should be doubled or tripled to give the capacities of the duplex or triplex pumped packages.

Note: The MFP14-PPU packages are not supplied with a connecting condensate return manifold. Ideally each pump should have its own dedicated return line to a vented receiver or holding tank. If the duplex pump returns are to be joined together to create a collective return line, care should be taken to ensure that it is adequately sized to accommodate the instantaneous discharge rate of all pumps discharging at the same time. Failure to do this may result in reduced capacity of the packaged pump unit.

Capacities

The capacity charts are based on a filling head of 0.3 m. The lift lines represent the net effective lift (i.e. lift plus frictional resistance).



Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions supplied with the unit.

Installation points to consider

As well as the returning condensate lines to and from the MFP14-PPU, consideration should be taken to ensure that the receiver vent and overflow pipes can be fitted to the recommended guidelines. Details are shown within the installation and maintenance instructions IM-P681-02.

Spare parts

For availability of spare parts refer to the individual product TI sheets that comprise the unit.

How to specify

Spirax Sarco MFP14-PPU vented automatic pump packaged unit operated by steam to 13.8 bar g. The complete system shall be supplied with a receiver designed to be compliant with the Pressure Equipment Directive (PED), and all welding in accordance with EN 287/288 BS EN Part 1 – 2004 and BS EN ISO 15614 Part 1 2004. The whole system shall be supplied ready to fit with a base plate.

How to order - Please state on the order if you require the optional loop seal.

Example: 1 off Spirax Sarco DN80 X DN50 MFP14-PPU (vented) automatic pump packaged unit with flanged PN16 external connections.