

spirax sarco

Cast Steel Float & Thermostatic Steam Traps FTB Super Capacity Series

The trap contains a float valve mechanism which modulates to discharge condensate continuously at steam temperature. Non-condensable gases are released by a separate internal balanced pressure thermostatic air vent.


Model	FTB-125	FTB-200
PMO	125 psig	200 psig
Sizes	2-1/2"	
Connections	NPT, SW	
Construction	Cast Steel Body	
	Stainless Steel valve head & seat, Mechanism housing	
Options	Bimetal Air Vent	

Typical Applications

All process heat exchange equipment, particularly when controlled by modulating temperature control valves; unit heaters and air heating coils.

Construction Materials

No.	Part	Material	
1	Body	Cast Steel	ASTM A216 WCB
2	Cover Screws	Carbon Steel	ASTM A449 Type 1
3	Cover Gasket	Graphite	
4	Cover	Cast Steel	ASTM A216 WCB
5	Valve Seat	Stainless Steel	
6	Valve Assembly Gasket	Graphite	
7	Main Valve Assembly Screws	Stainless Steel	
8	Ball Float	Stainless Steel	
9	Air Vent Assembly	Stainless Steel	
	Air Vent Head	Stainless Steel	
	Air Vent Seat	Stainless Steel	
15	Main Valve Assy Housing	Stainless Steel	
16	Pivot Pin	Stainless Steel	
17	Valve Head	Stainless Steel (FTB-175) Cast Stainless Steel (FTB-125)	
18	Float Arm	Stainless Steel (FTB-175)	



For Capacities, see TI-2-317-US

Limiting Operating Conditions

Max. Operating Pressure (PMO) FTB-125: 125 psig (8.6 barg)
FTB-200: 200 psig (13.8 barg)

Thermostatic air vent operating range	
Steam pressure (psig)	Maximum steam temperature °F
200	572
175	558
150	555
100	547
75	542
50	534
25	521
0	464

Note: Use bimetal air vent outside range on chart up to 650°F

Pressure Shell Design Conditions

PMA Max. allowable pressure FTB-125 } 200 psig/up to 650°F
FTB-200 } 12.1 barg/up to 343°C

TMA Max. allowable temp. FTB-125 } 650° F/0-200 psig
FTB-200 } 343°C/0-12.1 barg

Local regulation may restrict the use of this product below the conditions quoted. Limiting conditions refer to standard connections only. In the interests of development and improvement of the product, we reserve the right to change the specification.

Cast Steel Float & Thermostatic Steam Traps

FTB Super Capacity Series

Installation

A pipeline strainer should be installed ahead of any steam trap. Full-port isolating valves should be placed to permit servicing. The trap should be installed below the drainage point of the equipment with a collecting leg before the trap, in a position with the float arm in a horizontal plane so that the float rises and falls vertically, and with the direction of flow as indicated on the cover. Refer to IMI 2.300 for complete instructions.

Maintenance

This product can be maintained without disturbing the piping connections. Complete isolation from both supply and return line is required before any servicing is performed. The trap should be disassembled periodically for inspection and cleaning of the valve head and seat, and operating mechanism.


Worn or damaged parts should be replaced using a complete valve mechanism assembly and/or air vent assembly.

Complete installation and maintenance instructions are given in IMI 2.300, which accompanies the product.


Sample Specification

Steam traps shall be of the mechanical float type having cast steel bodies, NPT or SW connections, and stainless steel valve heads and seats. Incorporated into the trap body shall be a stainless steel balanced pressure thermostatic air vent capable of withstanding 572°F operating temperature and resisting waterhammer without sustaining damage. Internals of the trap shall be completely servicable without disturbing the piping. Trap tested in accordance to ANSI / FCI 85-1. Capacity data obtained in accordance to PTC 39.1.

Dimensions (nominal) in inches and millimeters							
Type & Size	A	B	C	D	E	F	Weight
FTB-125 2-1/2"	15.4 390	9.25 235	6.9 184	1.4 35	14.4 397	4.0 95	112 lb 50.8 kg
FTB-200 2-1/2"	15.4 390	9.25 235	6.9 184	1.4 35	14.4 397	4.0 95	112 lb 50.8 kg



2-1/2" FTB-125 & 200



Spare Parts

Gasket Kit (3 of each)	B, E (F)
Air Vent Kit	H, J, L, M, N
Valve Mechanism Kit (less float)	D, E, F
Float	P

**We certify that the data as given
on this sheet are correct.**

Signed: _____

Date: _____