

# CS10-1

## Stainless steel clean steam separator

### An effective solution to ensure steam dryness

The CS10-1 is designed to remove contaminants, entrained moisture and condensate from clean and pure steam systems for critical applications. The CS10-1 ensures a minimum steam dryness of 95% which is key to successful sterilization cycles and helps you achieve compliance with industry standards such as EN 285, HTM 2010 and AAMI-ST79.

The CS10-1 has been developed to solve problems associated with wet steam, its impact on sterilization and autoclave processes as well as limiting damage to downstream control valves and equipment.

#### Key features

- Designed to ensure steam dryness values above 95%.
- Designed in accordance with the ASME BPE guide for the biopharmaceutical industry.
- Protects and maintains service life of downstream pipeline equipment.
- Unique removable baffle plate to facilitate internal inspection.
- Minimal pressure drop.
- Internal surface finish of 0.5  $\mu\text{m}$  Ra electro-polished.
- Traceable 316L stainless steel material.
- FDA compliant seals.
- Part of a dedicated high purity product range from Spirax Sarco.




The **CS10-1** helps you achieve **compliance and quality** within your clean and pure steam system whilst maintaining **reliable operation** and **minimizing maintenance and downtime costs.**

## The range and options

Type	Size	Surface finish	Welds	Connections
CS10 - 1	½" - 2"	<b>Internal:</b> 0.5 µm Ra electro-polished <b>External:</b> 1.6 µm Ra satin bleed blast	Ground smooth and polished	Sanitary clamp or Tube weld ends

## Typical application



**spirax  
sarco**

Spirax-Sarco Limited, Charlton House, Cheltenham,  
Gloucestershire, GL53 8ER, UK  
T +44 (0)1242 521361  
F +44 (0)1242 573342  
E [enquiries@uk.spiraxsarco.com](mailto:enquiries@uk.spiraxsarco.com)